

# 3M™ Qualitative Fit Test Apparatus

The 3M Qualitative Fit Test Apparatus offers a simple way to meet the Occupational Safety and Health Administration's (OSHA) qualitative fit testing requirements (1910.134, Appendix A). It can be used to assess the face-to-respirator seal of any particulate respirator or gas/vapor respirator with a particulate filter.

Fit testing is accomplished by spraying a test agent into the hood environment with the respirator in place. If the wearer does not detect the taste of the test agent, an acceptable fit has been demonstrated.














## Some benefits of 3M's Fit Test Apparatus:

- Fast, easy method for performing qualitative fit testing
- Two test agent options are available to determine employee's taste threshold to test solution – 3M™ Qualitative Fit Test Apparatus FT-10, Sweet and 3M™ Qualitative Fit Test Apparatus FT-30, Bitter
- Can be used with any particulate respirator, or any gas/vapor respirator with particulate filter
- Convenient, reliable and economical to use
- Provides consistent test atmosphere for test exercises
- Educational materials available from 3M to help you meet OSHA respirator program requirements

## Ordering Information

	Cat. No.	Description	Size	Each/Case
	FT-10	3M™ Qualitative Fit Test Apparatus (sweet) Contains: FT-11, FT-12, FT-14, FT-15 (1 each); FT-13 (2 each)		1
	FT-30	3M™ Qualitative Fit Test Apparatus (bitter) Contains: FT-31, FT-32, FT-14, FT-15 (1 each); FT-13 (2 each)		1
	FT-11	Sensitivity Solution (sweet)	55 mL	6
	FT-12	Fit Test Solution (sweet)	55 mL	6
	FT-31	Sensitivity Solution (bitter)	55 mL	6
	FT-32	Fit Test Solution (bitter)	55 mL	6
	FT-13	Nebulizer		3
	FT-14	Test Hood (2/pack)		10
	FT-15	Collar		1

### Training, Fit Testing and Technical Service

Ask your 3M sales representative about our related educational materials and services to help you meet OSHA training regulations for the use of respirators. Or call our technical service line at: 1-800-243-4630, opt. 3. Outside the U.S., contact your local 3M subsidiary.

For more information call 1-888-3M-HELPS or visit our website at [3M.com/workersafety](http://3M.com/workersafety)



**Personal Safety Division**  
3M Center  
Building 235-2NW-70  
St. Paul, MN 55144-1000

**3M Canada Company PSD**  
P.O. Box 5757  
London, Ontario N6A 4T1  
Canada

3M is a trademark of 3M Company,  
used under license in Canada.  
Please recycle. Printed in USA. © 3M 2019.  
70-2008-6699-7